

Rosemount Manifolds

- *Factory assembled, leak-tested, and calibrated*
- *Full breadth of offering including integral, conventional, and inline designs*
- *Integral design enables “flangeless” valve integration*
- *2, 3, and 5 valve configurations*
- *Compact, lightweight design*
- *Easy in-process calibration*
- *Direct-mount capability*



Contents


Rosemount Manifolds Selection Guide	page 2
Valve Configuration	page 3
Ordering Information	page 5
Specifications	page 11
Dimensional Drawings.	page 17

Rosemount Manifolds Selection Guide

ROSEMOUNT 304 CONVENTIONAL MANIFOLD

See "Options" on page 27.

- Attaches to transmitter flange
- 2, 3, and 5-valve configurations
- Traditional (Flange x Flange, Flange x NPT) & Wafer styles
- Factory assembled, seal-tested, and calibrated



Rosemount 304 Conventional Manifold-Traditional Style



Rosemount 304 Conventional Manifold-Wafer Style

ROSEMOUNT 305 INTEGRAL MANIFOLD

See "Options" on page 27.

- Assembles directly to transmitter, eliminating need for flange
- 2, 3, and 5-valve configuration
- Available in Coplanar™ and traditional styles
- Compact, lightweight assembly
- Factory assembled, seal-tested, and calibrated
- 50% fewer leak points than conventional transmitter / flange / manifold interface



Rosemount 305 Integral Manifold Coplanar Style

ROSEMOUNT 306 INLINE MANIFOLD

See "Options" on page 27.

- Assembled directly to inline pressure transmitters
- Block-and-Bleed and 2-valve configurations
- Male or Female threaded NPT process connection




Rosemount 306 Inline Manifold

Valve Configuration

BLOCK-AND-BLEED

The block-and-bleed configuration is available on the Rosemount 306 Manifold for use with inline gage and absolute pressure transmitters. A single block valve provides instrument isolation and a plug provides drain/vent capabilities.


306 Manifold




TWO-VALVE

The two-valve configuration is available on Rosemount 304, 305, and 306 Manifolds for use with absolute and gage pressure transmitters. A block valve provides instrument isolation and a drain/vent valve allows venting, draining, or calibration.

304 Manifold




305 & 306 Manifolds




THREE-VALVE

The three-valve configuration is available on Rosemount 304 and 305 Manifolds for use with differential pressure and multivariable transmitters. Two block valves provide instrument isolation, and one equalize valve is positioned between the high and low transmitter process connections.


304 (Traditional) Manifold



304 (Wafer) Manifold



305 Manifold



NOTE

Test/Vents receive plastic caps to protect threaded connections unless otherwise noted.

NOTE


Test (Plugged) connections receive 1/4-in. NPT plugs unless otherwise noted.

Rosemount Manifolds

FIVE-VALVE

The five-valve configuration is available on Rosemount 304 and 305 Manifolds for use with differential pressure and multivariable transmitters. Two block valves provide instrument isolation and one equalize valve is positioned between the high and low transmitter process connections. In addition, two drain/vent valves allow for controlled venting, 100% capture of vented or drained process, and simplified in-process calibration capability.


304 (Wafer) & 305 Manifolds



FIVE-VALVE NATURAL GAS

The five-valve natural gas configuration is available on the Rosemount 304 and 305 Manifolds for use with differential pressure and multivariable transmitters. Two block valves provide instrument isolation and a single drain/vent valve allows for controlled venting, 100% capture of vented or drained process, and simplified in-process calibration capability. In addition, two equalize valves provide extra protection from leaking to ensure DP signal integrity.

304 (Traditional) & 305 Manifolds



NOTE

Test/Vents receive plastic caps to protect threaded connections unless otherwise noted.

NOTE

Test (Plugged) connections receive 1/4-in. NPT plugs unless otherwise noted.

Ordering Information

Rosemount Manifolds can be ordered as a stand-alone product or as an integrated assembly that is attached to a transmitter.

Stand-Alone Manifold:

1. Reference the “Rosemount Manifolds Selection Guide” (see page 2) for assistance on choosing the type of manifold needed.
2. Specify a completed model number by referencing the applicable ordering table for the selected manifold type:
 - a. Rosemount 304 Conventional Manifold, see page 6.
 - b. Rosemount 305 Integral Manifold, see page 8.
 - c. Rosemount 306 Inline Manifold, see page 10.

Transmitter / Manifold Assembly:

1. Specify a completed Rosemount transmitter model number by referencing the applicable product data sheet.
2. Specify a completed manifold model number by referencing the applicable ordering table for the selected manifold type:
 - a. Rosemount 304 Conventional Manifold, see page 6.
 - b. Rosemount 305 Integral Manifold, see page 8.
 - c. Rosemount 306 Inline Manifold, see page 10.
3. Verify the transmitter model number contains the correct “Process Connection” code or “Manifold Option” code for the desired transmitter manifold assembly (see Table 1).

Table 1. Ordering Codes for a Transmitter / Manifold Assembly

Transmitter	Manifold	Process Connection Code	“Manifold” Option Code
3051S	304	A12	—
	305	A11	—
	306	A11	—
3051/2051/3095	304	—	S6
	305	—	S5
	306	—	S5
1151	304	S6	—
	305	—	—
	306	—	—
2088	304	—	—
	305	—	—
	306	—	S5

Rosemount Manifolds



Rosemount 306 Inline Manifolds

Table 4. Rosemount 306 Inline Pressure Manifold Ordering Information

★ The Standard offering represents the most common options. The starred options (★) should be selected for best delivery. The Expanded offering is subject to additional delivery lead time.

Model	Product Description			
0306	Pressure Manifold			
Manufacturer				
Standard				Standard
R	Rosemount Inc.			★
Manifold Style				
Standard				Standard
T	Threaded			★
Manifold Type				
Standard				Standard
1	Block and bleed			★
2	2-valve			★
Expanded				
3 ⁽¹⁾	2-valve (per ASME B31.1 Power Piping Code)			
	Body	Bonnet	Stem and Tip / Ball	
Standard				Standard
2	316 SST	316 SST	316 SST	★
Expanded				
3 ⁽²⁾⁽³⁾	Alloy C-276	Alloy C-276	Alloy C-276	
Process Connection				
Standard				Standard
AA	1/2–14 male NPT			★
BA ⁽²⁾	1/2–14 female NPT			★
Packing Material				
Standard				Standard
1	PTFE			★
Expanded				
2 ⁽⁴⁾	Graphite-based			
Valve Seat				
Standard				Standard
1	Integral			★

Options

Cleanings			
Expanded			
P2 ⁽⁵⁾	Cleaning for special services		
Material Recommendations for NACE			
Standard			Standard
SG ⁽³⁾⁽⁶⁾	Sour Gas (Meets NACE MR 0175 / ISO 15156, MR 0103)		★
Typical Integral Manifold Model Number: 3 0 6 R T 2 2 B A 1 1			
Typical Transmitter Model Number: 3051TG3A2B21AS5B4			

(1) Only available with 316 SST materials of construction and graphite-based packing.

(2) Not available with block-and-bleed manifold type

(3) Materials of Construction comply with recommendations per NACE MR0175/ISO 15156 for sour oil field production environments. Environmental limits apply to certain materials. Consult latest standard for details. Selected materials also conform to NACE MR0103 for sour refining environments.

(4) Includes graphite tape on plugs.

(5) Not available with Graphite-Based Packing Material code 2.

(6) Only available with 316 SST material of construction code 2. Manifolds with SG option are built with 316 SST body and bonnets; Alloy C-276 stems, tips/balls.

Product Data Sheet

00813-0100-4733, Rev NB

January 2011

Rosemount Manifolds

Figure 3. 306 Integral Manifolds - Pressure vs. Temperature




Table 7. 306 Integral Manifolds - Pressure and Temperature Ratings

Packing	Seat	Pressure and Temperature Ratings
PTFE	Integral	10000 psi @ 85 °F (689 bar @ 29 °C) 4000 psi @ 400 °F (276 bar @ 204 °C)
Graphite	Integral	6000 psi @ 200 °F (414 bar @ 93 °C) 1500 psi @ 750 °F (103 bar @ 399 °C)
Graphite (ASME B31.1)	Integral	6000 psi @ 100 °F (414 bar @ 38 °C) 2915 psi @ 1000 °F (201 bar @ 538 °C)

Rosemount Manifolds

Process Connections

Table 8. Process Connections

Model and Style	Connection
304 Flange by Pipe Flange by Flange Wafer	$\frac{1}{2}$ - 14 Female NPT $2\frac{1}{8}$ -in. (54 mm) center-to-center connection (Process Adapters required) $\frac{1}{2}$ - 14 Female NPT <u>Process Adapters</u> $\frac{1}{2}$ - 14 Female NPT Flange Adapter $\frac{1}{2}$ -in. Ferrule Flange Adapter 12-mm Ferrule Flange Adapter
305 Coplanar Traditional	$\frac{1}{2}$ - 14 Female NPT $\frac{1}{4}$ - 18 Female NPT (Process Adapters optional) <u>Optional Process Adapters</u> $\frac{1}{2}$ - 14 Female NPT Flange Adapter 12 mm Ferrule Flange Adapter
306 Block-and-Bleed 2-Valve	$\frac{1}{2}$ - 14 Male NPT $\frac{1}{2}$ - 14 NPT (Male or Female)

Instrument Connections

Table 9. Manifold - Transmitter Interface

Model	Connection
304	Mounted to traditional transmitter flange, $2\frac{1}{8}$ -in. (54 mm) center-to-center connection per IEC 61518, Type B shut-off device (without SPIGOT)
305	Mounted directly to Coplanar sensor module of transmitter, 1.3-in. (287 mm) center-to-center process isolators
306	$\frac{1}{2}$ - 14 Male NPT

Test / Vent Connections

$\frac{1}{4}$ -18 Female NPT

Manifold Bolts

Standard material is plated carbon steel per ASTM A449, Type 1

Alternative bolt materials offered through Option Codes

- L4 Austenitic 316 Stainless Steel Bolts
- L5 ASTM-A-193, Grade B7M Bolts
- L8 ASTM-A-193, Class 2, Grade B8M Bolts

Product Data Sheet

00813-0100-4733, Rev NB

January 2011

Rosemount Manifolds

O-Rings

Figure 4. 304 Manifold O-Rings

Manifold-to-Flange O-Rings

Same material as specified by manifold "Packing Material" selection:

- "1" = PTFE
- "2" = Graphite

Flange Adapter O-Rings

Glass-filled PTFE




Figure 5. 305 Manifold O-Rings

Sensor Module-to-Manifold O-Rings

Specified in the transmitter model number




Table 10. 304 Conventional Manifolds - Process Wetted Materials of Construction

Component	SST	CS	SST with SG Option	
Body	316 SST	CS	316 SST	
Ball / Tip	316 SST /316Ti SST	316 SST	Alloy C-276	
Stem	316 SST	316 SST	Alloy C-276	
Packing	PTFE / Graphite	PTFE	PTFE / Graphite	
Bonnet	316 SST	316 SST	316 SST	
Pipe Plug	316 SST	CS	316 SST	

Table 11. 305 Integral Manifolds - Process Wetted Materials of Construction


Component	SST	Alloy C-276	316 SST with SG option	
Body	316 SST	Alloy C-276	316 SST	
Ball / Tip	316 SST /316Ti SST	Alloy C-276	Alloy C-276	
Stem	316 SST	Alloy C-276	Alloy C-276	
Packing	PTFE / Graphite	PTFE / Graphite	PTFE / Graphite	
Bonnet	316 SST	Alloy C-276	316 SST	
Pipe Plug	316 SST	Alloy C-276	316 SST	
Drain / Vent Valve	316 SST	Alloy C-276	Alloy C-276	

Table 12. 306 Inline Manifolds - Process Wetted Materials of Construction

Component	SST	Alloy C-276	316 SST with SG option	
Body	316 SST	Alloy C-276	316 SST	
Ball / Tip	316 SST /316Ti SST	Alloy C-276	Alloy C-276	
Stem	316 SST	Alloy C-276	Alloy C-276	
Packing	PTFE / Graphite	PTFE / Graphite	PTFE / Graphite	
Bonnet	316 SST	Alloy C-276	316 SST	
Pipe Plug	316 SST	Alloy C-276	316 SST	
Bleed Screw	316 SST / 316Ti SST	Alloy C-276	Alloy C-276	

Materials of Construction - Typical

Figure 6. Typical Rosemount Manifold Valve




Estimated Weight


Model and Description	Weight
304	
2-valve traditional flange x NPT	5.0 lbs (2.3 kg)
2-valve traditional flange-x flange	5.5 lbs (2.5 kg)
3-valve traditional flange x NPT	5.2 lbs (2.4 kg)
3-valve traditional flange x flange	5.7 lbs (2.6 kg)
3-valve wafer flange x NPT	4.0 lbs (1.8 kg)
5-valve wafer flange x NPT	5.7 lbs (2.6 kg)
5-valve traditional flange x NPT	5.7 lbs (2.6 kg)
5-valve traditional flange x flange	5.7 lbs (2.6 kg)
305	
2-valve Coplanar	4.5 lbs (2.0 kg)
2-valve traditional	6.0 lbs (2.7 kg)
3-valve Coplanar	4.7 lbs (2.1 kg)
3-valve traditional	6.0 lbs (2.7 kg)
5-valve Coplanar	6.5 lbs (3.0 kg)
306	
Block-and-Bleed	1.1 lbs (0.5 kg)
2-valve	2.5 lbs (1.1 kg)

Rosemount 306R Pressure Style Manifold (3051S_T Shown)

BLOCK AND BLEED STYLE



TWO-VALVE STYLE




Manifold valve orientation may vary with respect to transmitter mounting holes.


Dimensions are in inches (millimeters)

Installations for Rosemount 3051T and 3051S_T Transmitters for Panel Mounting

ROSEMOUNT 3051T




ROSEMOUNT 3051S_T



Manifold valve orientation may vary with respect to transmitter mounting holes.

Dimensions are in inches (millimeters)


Installations for Rosemount 3051T and 3051S_T Transmitters for 2-in. Pipe Mounting



Manifold valve orientation may vary with respect to transmitter mounting holes.


Dimensions are in inches (millimeters)

Coplanar Manifold with Optional Bracket for 2-in. Pipe Mounting




Dimensions are in inches (millimeters)

Traditional Manifold with Optional Brackets for 2-in. Pipe Mounting



Dimensions are in inches (millimeters)

VS/VVC Heavy Duty Manifold Mounting Bracket




Dimensions are in inches (millimeters)

OPTIONS

Module Guard

A sensor module guard is available to protect the transmitter process isolating diaphragms. This guard should be used whenever the transmitter is removed from the integral manifold to avoid damage to the isolating diaphragms.

- Part number: 00305-1000-0001 (5/pack)



P2 Cleaning for Special Services

Per ASTM G93-96, this option minimizes process contaminants by cleaning wetted surfaces with a suitable detergent.

SG Sour Gas

Materials of Construction comply with recommendations per NACE MR 0175/ISO 15156 for sour oil field production environments. Environmental limits apply to certain materials. Consult latest standard for details. Selected materials also conform to NACE MR0103 for sour refining environments.

Heat Block Kits

Rosemount 304 Manifolds are available with steam heat block kits for cold environments and services. The steam block attaches directly to the manifold to prevent the process from freezing.

ASME B31.1 Power Piping Code

Rosemount Manifolds are available in configurations that meet the requirements of the ASME B31.1 Power Piping Code. This code specifies design criteria for most air, gas, steam, water, and oil systems used in electric generating systems, central and district heating systems, industrial power plants, and geothermal plants. ASME B31.1 includes requirements for manifolds, valves, and piping. Transmitters and other measuring devices do not fall within the scope of this code.

Marking

Manifolds are tagged with a part number, schematic drawing, temperature, and pressure limits.

Other Publications

For additional information, go to www.rosemount.com.

Rosemount Manifolds

Product Data Sheet

00813-0100-4733, Rev NB

January 2011

SPARE PARTS LIST

Table 13. Rosemount 304 Conventional Manifold

Part Description	Part Number (Traditional Style)	Part Number (Wafer Style)
Mounting Brackets (qty. 1)		
Manifold Heavy Duty Mounting Bracket, CS	01166-8005-0002	NA
Manifold Heavy Duty Mounting Bracket, SST	01166-8005-0001	NA
Manifold SST Mounting Bracket for 2-in. Pipe Mount	NA	00305-0405-0001
O-Rings (set of 12)		
Manifold-to-Flange O-Ring, Glass-filled PTFE	03031-0019-0003	03031-0019-0003
Manifold-to-Flange O-Ring, Graphite-filled PTFE	03031-1302-0002	03031-1302-0002
Manifold-to-Flange Bolt Kits (set of 4)		
Consult factory for part numbers	Consult Factory	Consult Factory
Heater Block Kits (qty. 1)		
Steam Block Kit	00305-0406-0001	NA

Table 14. Rosemount 305 Integral Manifold

Part Description	Part Number (Traditional Style)	Part Number (Coplanar Style)
Mounting Brackets (qty. 1)		
Manifold SST Mounting Bracket for 2-in Pipe Mount	NA	00305-0405-0001
Bolt Kits (set of 4)		
CS Bolt Kit	03031-0312-0001	03031-0311-0001
SST Bolt Kit	03031-0312-0002	03031-0311-0002
ANSI/ASTM-A-193-B7M Bolt Kit	03031-0312-0003	03031-0311-0003
Drain/Vents (qty. 1)		
316 SST Drain/Vent for use with 3-valve 305 Manifold	01151-0028-0012	01151-0028-0012
Alloy C-276 Drain/Vent for use with 3-valve 305 Manifold	01151-0028-0013	01151-0028-0013
Coplanar Flange Kits (qty. 1)		
Differential Flange Kit, SST	NA	00305-1001-0001
Gauge Flange Kit, SST	NA	00305-1001-1001
O-Rings (set of 12)		
Manifold-to-Module O-Ring, Glass-filled PTFE	03031-0234-0001	03031-0234-0001
Manifold-to-Module O-Ring, Graphite-filled PTFE	03031-0234-0002	03031-0234-0002
Sensor Guard (set of 5)		
Coplanar Module Sensor Guard	00305-1000-0001	00305-1000-0001

Rosemount Manifolds

Product Data Sheet

00813-0100-4733, Rev NB

January 2011

Standard Terms and Conditions of Sale can be found at www.rosemount.com/terms_of_sale
The Emerson logo is a trade mark and service mark of Emerson Electric Co.
Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc.
Coplanar is a trademark of Rosemount Inc.
© 2010 Rosemount, Inc. All rights reserved.

**Emerson Process Management
Rosemount Measurement**
8200 Market Boulevard
Chanhassen MN 55317 USA
Tel (USA) 1 800 999 9307
Tel (International) +1 952 906 8888
Fax +1 952 949 7001

Emerson Process Management
Blegistrasse 23
P.O. Box 1046
CH 6341 Baar
Switzerland
Tel +41 (0) 41 768 6111
Fax +41 (0) 41 768 6300

Emerson FZE
P.O. Box 17033
Jebel Ali Free Zone
Dubai UAE
Tel +971 4 811 8100
Fax +971 4 886 5465

**Emerson Process Management Asia Pacific
Pte Ltd**
1 Pandan Crescent
Singapore 128461
Tel +65 6777 8211
Fax +65 6777 0947
Service Support Hotline : +65 6770 8711
Email : Enquiries@AP.EmersonProcess.com



نیک تک بهسازان کهن (سهامی خاص)
تامین و تولید ابزارآلات دقیق و کنترل صنعتی

تهران - خیابان بخارست - کوچه یکم - پلاک ۱۹

طبقه همکف کدپستی ۱۵۱۳۶-۳۸۳۱۳

☎ 021- 88100370 ✉ info@niktec.ir



برای خرید
اسکن کنید



EMERSON
Process Management